



DIRECT
SUPPLY INC
SURFACE MATERIALS \ CABINETRY \ HARDWARE

DutchLock Adhesive & Accessories

SEAMLOCK PRO

SeamLockPRO is a two-part methacrylate, DRIPLESS seaming adhesive designed for the Inconspicuous bonding of various substrates, including solid surface (acrylic, polyester, and blended products), granite, engineered stone, quartz, marble, cultured marble, glass, sintered stone, porcelain, and various plastics (not low energy surfaces).

- DRIPLESS
- KNIFE-ABLE
- SAND-ABLE
- BLADE-ABLE
- AVAILABLE IN 500+ COLORS

Scan me to visit
dutchlockadhesives.com to
find your perfect match!



STOCKED 250ML COLORS

- | | | |
|-------------------|-------------------------|--------------------------|
| • ALUMINUM - 642 | • DUNE - 310 | • MISTY - 220 |
| • BEACH - 230 | • EARTH BROWN - 820 | • NATURAL - 214 |
| • BEIGE - 228 | • FOG - 200 | • NEUTRAL - 868 |
| • CAMEO - 120 | • GLACIER - 111 | • NEWPORT GREY - 869 |
| • CHALK - 100 | • I-BONE - 816 | • PEWTER - 518 |
| • CHAMELEON - 800 | • ICE -218 | • SAND - 216 |
| • CLAY - 526 | • I-PUDDING BROWN - 846 | • STONE - 222 |
| • CLEAR - 199 | • MARBLE - 106 | • TRANSPARENT WHITE- 825 |
| • CLOUD - 118 | • MESA - 604 | • WINTER - 101 |
| • DESIGN - 601 | • MIDNIGHT - 532 | |

- [DL-DISPENSER-250-MANUAL | GUN](#)
- [DL-MIXING TIP-250/500 | BULK TIPS](#)
- [CONTACT US FOR PRICING ON 50ML & 500ML CARTRIDGES](#)

NON STOCK ADHESIVES

Order By Color & Size - No Minimum Order or Surcharges!



SeamLock PRO dripless adhesive reduces waste and saves on cleanup! Standard Flowable Version SeamLock also available!



1055 36th Street SE, Grand Rapids, MI 49508

www.directsupplyinc.com | P: 616-245-4415 | sales@directsupplyinc.com



DIRECT
SUPPLY INC
SURFACE MATERIALS \ CABINETRY \ HARDWARE

DutchLock Adhesive & Accessories

SUBSTRATE BONDER

Sub Lock SB-100 is a two-part, unfilled, room temperature cure, urethane adhesive designed to bond Quartz, Solid Surface, Natural and Engineered Stone to wood, particle board, plywood, or other substrates. Sub Lock is strong but highly flexible in nature with a rapid cure. It is specially formulated for a 1:1 mix ratio for use in side-by-side cartridges, or to be used by hand mixing, or use with Meter Mix Equipment. Substrate Bonder is Low VOC and is non-flammable. A handling cure is typically achieved at room temperature within 30 minutes.

- DL-SUB100-200 | 200ML CARTRIDGE
- DL-SUB100-400 | 400ML CARTRIDGE
- DL-DISPENSER-200-MANUAL | GUN
- DL-DISPENSER-400-MANUAL | GUN
- DL-MIXING TIP-200/400 | BULK TIPS



ROD & CLIP BONDER

BD-300 - 1:1 Ratio - Used for Bonding and Adhering steel and fiberglass rods into granites, stones, marbles, and other natural and synthetic countertop materials.

BD-466 - 10:1 Ratio - Used for Bonding and Adhering steel and fiberglass rods into granites, stones, marbles, and other natural and synthetic countertop materials.

- DL-BD300-400 | 400ML - 1:1 CARTRIDGE
- DL-BD466-500 | 500ML - 10:1 CARTRIDGE
- DL-DISPENSER-400-MANUAL | GUN
- DL-MIXING TIP-200/400 | BULK TIPS
- DL-DISPENSER-500-MANUAL | GUN
- DL-MIXING TIP-250/500 | BULK TIPS



GRANITE FABRICATION TIP: 3/16" Minimum channel width and 3/8" maximum depth to ensure the bond does not pull in the granite face





DIRECT
SUPPLY INC
SURFACE MATERIALS \ CABINETRY \ HARDWARE

DutchLock Adhesive & Accessories

REVOLSEAM PRO Knife Grade Adhesive for Hard Surfaces

High-quality adhesive delivers maximum seam strength with a 10-minute work time and gel time. Its easy application allows you to quickly select and mix a match to fabricate with confidence.

THREE STEP PROCESS

Great for white base colors

1. Resin - Crystal Clear or Chameleon

Available in Two Liter Pouch or 5 Gallon Pails

FLOWING CRYSTAL

DL-SKI000FLCR-GAL

DL-SKI000FLCR-POUCH

PRO CRYSTAL

DL-SKI500KGCR-GAL

DL-SKI500KGCR-POUCH

PRO CHAMELEON

DL-SKI800KGCM-GAL

DL-SKI800KGCM-POUCH



Comes with
1 Hardener
10 4oz Mix Cups
10 Mixing Sticks

2. Hardener - 2oz easy to dispense bottle.

No measuring mysteries!

DL-SK5020-2

DL-SK5020 16 - 1LB

DL-RSP-STARTER

Toolbox

Directometer Color Kit

(1) Quart Crystal Resin

Also Available
in Bulk!

(1) Quart Chameleon Resin

(2) Hardeners

(10) of the Most Popular Pigments

SIZE

2 OZ

16 OZ



3. Pigment - 2oz easy to dispense bottle.

No mess dispensing!

Available Pigments

• ARCTIC 2 - 101	• COCOA 2 - 323	• MESA 2 - 604	• SHALE 2 - 525
• BEACH 2 - 230	• CREAM 2 - 232	• MIDNIGHT 2 - 532	• SLATE 2 - 512
• BEIGE 2 - 228	• DUNE 2 - 310	• MISTY 2 - 220	• SONORA 2 - 317
• BRILLIANT 2 - 103	• FAWN 2 - 316	• MOCHA 2 - 322	• STONE 2 - 222
• BUFF 2 - 210	• FIRE 2 - 621	• NATURAL 2 - 214	• THUNDER 2 - 522
• BUTTER 2 - 226	• ICE 2 - 218	• NEWPORT 2 - 116	• WILLOW 2 - 314
• CANVAS 2 - 112	• LATTE 2 - 312	• PEARL 2 - 510	
• CARAMEL 2 - 234	• LAVA 2 - 521	• PEWTER 2 - 518	
• CHOCOLATE 2 - 324	• MARBLE 2 - 106	• PRAIRIE 2 - 518	



CHECK OUT ALL OF OUR FORMULAS ONLINE AT REVOLSEAMPRO.COM

1055 36th Street SE, Grand Rapids, MI 49508

www.directsupplyinc.com | P: 616-245-4415 | sales@directsupplyinc.com



DIRECT
SUPPLY INC
SURFACE MATERIALS \ CABINETRY \ HARDWARE

DutchLock Adhesive & Accessories

DIRECTOMETER ADHESIVE COLOR MATCHING KIT

Quickly find your match!

- Comes with (2) color chip chains
- Color Muse Device
- Syncs with your phone and provides you with the best match via the DutchLock app!

Still, trying to decide what color is the perfect match for your countertop surface? Simply place the muse on the counter and it will provide three top matches in the DutchLock app. Use the chains to match up which one is the closest match!



STEPS:

1. Calibrate in cover
2. Place on surface
3. Review matches on the sample chain
4. Mix the best match!

DL-Color Matching Kit

Follow the formula for guess free matching

DUTCHLOCK TAPE Save time and clean up most of the excess glue prior to curing.

One side Satin / One side Matte (double sided tape)

200-foot roll!

DL-Dutchlock Tape



STEPS:

1. Fill seam
2. Place tape above the seam
3. Blade off excess glue with tape over the seam
4. Remove tape, blade off excess glue around cured flat seam

Match your seam to the surface' polish level

